

GENERAL NOTES


KEY

- LOCATED AT TOP FACE
- LOCATED AT BOTTOM FACE
- DIRECTION
- DUT IS POSITIVE

ABBREVIATIONS

- E EAST
- W WEST
- C CENTER
- UPP UPPER
- MID MIDDLE
- LOW LOWER
- BM BEAM
- COL COLUMN
- GUS GUSSET
- PL PLATE
- ROT ROTATION
- OUT OF PLANE
- CONN CONNECTION
- DISP DISPLACEMENT
- HORIZ HORIZONTAL
- VERT VERTICAL
- MIDPT MIDPOINT
- QRPT QUARTERPOINT

DESIGNATION



DESCRIPTION	RANGE +/-	FREEDOM	DESCRIPTION	RANGE +/-	FREEDOM
1 E ANCHOR PL SLIP	25mm		51 UPP W GUS DDP LOW EDGE	100mm	HORIZ
2 E ANCHOR PL UPLIFT	25mm		52 B4 DDP DISP AT MIDPT	800mm	HORIZ
3 E BASE PL SLIP	25mm		53 B2 2ND DDP DISP AT QRPT	250mm	HORIZ
4 E BASE PL UPLIFT	25mm		54 C GUS DDP W UPP EDGE	100mm	HORIZ
5 E COL ROT AT LOW GUS EDGE	50mm		55 C GUS DDP UPP W EDGE	100mm	HORIZ
6 E COL ROT AT LOW GUS EDGE	50mm		56 C GUS DDP UPP W C	100mm	HORIZ
7 MID BM FRAME DRIFT	300mm		57 C GUS DDP UPP C	25mm	HORIZ
8 E SHEAR CONN ROT MID BM	50mm		58 MID BM DDP ROT C GUS	25mm	HORIZ
9 E SHEAR CONN ROT MID BM	50mm		59		
10 E COL ROT AT UPP GUS EDGE	50mm		60 MID BM ROT AT C GUS E EDGE	50mm	
11 E COL ROT AT UPP GUS EDGE	50mm		61 MID BM ROT AT C GUS E EDGE	50mm	HORIZ
12 UPP BM FRAME DRIFT	400mm		62 MID BM DDP ROT C GUS W EDGE	25mm	HORIZ
13 UPP BM ROT AT E GUS EDGE	50mm		63 MID BM DDP ROT C GUS W EDGE	25mm	HORIZ
14 UPP BM ROT AT E GUS EDGE	50mm		64 C GUS DDP LOW C	25mm	HORIZ
15			65 VERT DISP MIDPT C GUS	50mm	HORIZ
16 UPP BM ROT AT W GUS EDGE	50mm		66 C GUS DDP LOW W C	100mm	HORIZ
17 UPP BM ROT AT W GUS EDGE	50mm		67 C GUS DDP LOW W EDGE	100mm	HORIZ
18 W COL ROT AT UPP GUS EDGE	50mm		68 C GUS DDP W LOW EDGE	100mm	HORIZ
19 W COL ROT AT UPP GUS EDGE	50mm		69 B2 DDP DISP AT QRPT	250mm	HORIZ
20 W SHEAR CONN ROT MID BM	50mm	70A	70 B2 DDP DISP AT MIDPT	800mm	HORIZ
21 W SHEAR CONN ROT MID BM	50mm		71 LOW W GUS DDP E EDGE	150mm	
22 W COL ROT AT LOW GUS EDGE	50mm		72 LOW W GUS DDP UPP EDGE	150mm	
23 W COL ROT AT LOW GUS EDGE	50mm		73 LOW W GUS DDP C	150mm	
24 W BASE PL UPLIFT	25mm		74 ACTUATOR BASE PL UPLIFT	25mm	
25 W BASE PL SLIP	25mm		75 ACTUATOR BASE PL SLIP	25mm	
26 W ANCHOR PL UPLIFT	25mm		76		
27 W ANCHOR PL SLIP	25mm		77		
28 LOW E GUS DDP C	150mm		78 B1 BRACE DIAGONAL	250mm	
29 LOW E GUS DDP UPP EDGE	150mm		79 B1 BRACE DIAGONAL	250mm	
30 LOW E GUS DDP W EDGE	150mm		80 B2 BRACE DIAGONAL	250mm	
31A B1 DDP DISP AT MIDPT	800mm		81 B2 BRACE DIAGONAL	250mm	
32 B1 DDP DISP AT QRPT	250mm		82 B3 BRACE DIAGONAL	250mm	
33 C GUS DDP LOW E EDGE	150mm		83 B3 BRACE DIAGONAL	250mm	
34 C GUS DDP E LOW EDGE	150mm		84 B4 BRACE DIAGONAL	250mm	
35 C GUS DDP LOW E CENTER	150mm		85 B4 BRACE DIAGONAL	250mm	
36			86 C GUS PLYWOOD DDP UPP RIGHT	50mm	
37 MID BM DDP ROT C GUS E EDGE	25mm		87 C GUS PLYWOOD DDP UPP LEFT	50mm	
38 MID BM DDP ROT C GUS E EDGE	25mm		88 C GUS PLYWOOD DDP LOW LEFT	50mm	
39 MID BM ROT AT C GUS E EDGE	50mm		89 C GUS PLYWOOD DDP LOW RIGHT	50mm	
40 MID BM ROT AT C GUS E EDGE	50mm				
41 C GUS DDP UPP E C	100mm				
42 C GUS DDP UPP E EDGE	100mm				
43 C GUS DDP UPP EDGE	100mm				
44 B1 2ND DDP DISP AT QRPT	250mm				
45 B3 DDP DISP AT MIDPT	800mm				
46 UPP E GUS DDP LOW EDGE	100mm				
47 UPP E GUS DDP W EDGE	100mm				
48 UPP E GUS DDP C	100mm				
49 UPP W GUS DDP C	100mm				
50 UPP W GUS DDP E EDGE	100mm				

TCBF1-TG: TOMORROW'S CONCENTRIC BRACED FRAME 1

NEES/SC NCREE BRACED FRAME TEST INSTRUMENTATION DRAWINGS

DRAWN BY: JAP

DESIGNED BY: JAP & KAC

CHECKED BY: KAC

DATE: APRIL 2, 2008

CONTACT: CROEBER@U.WASHINGTON.EDU

DWG:

IN-7